DLG Test Report 6921

RZB Rudolf Zimmermann, Bamberg GmbH PLANOX TUBE Farm

Resistance to ammonia, cleaning distance





Overview

A test mark "DLG-APPROVED for individual criteria" is awarded for agricultural products which have successfully fulfilled a scope-reduced usability testing conducted by DLG according to independent and recognized evaluation criteria. The test is intended to highlight particular innovations and key criteria of the test object. The test may contain criteria from the DLG test scope for overall tests, or focus on other value-



PLANOX TUBE FARM
Resistance to ammonia
Cleaning distance
DLG Test Report 6921

determining characteristics and properties of the test subject. The minimum requirements, test conditions and procedures as well as the evaluation bases of the test results will be specified in consultation with an expert group of DLG. They correspond to the recognized rules of technology, as well as scientific and agricultural knowledge and requirements. The successful testing is concluded with the publication of a test report, as well as the awarding of the test mark which is valid for five years from the date of awarding.

The ammonia resistance test was performed as a laboratory test according to the patented DLG test standard. This test is intended to determine the suitability of equipment for animal living areas to withstand the impacts of animal environments. The cleaning distance test assesses the suitability for cleaning animal living areas. Other criteria were not tested. As of 2017 the luminaires will be operated in the test chamber both passively (without power supply) as well as actively according to a determined test program.

Assessment – Brief Summary

The LED light "PLANOX TUBE Farm" has successfully completed the DLG test for ammonia resistance and cleaning distance.

According to this result, it can be assumed that these luminaires are resistant to the typical environmental conditions of animal living areas and that no accelerated reduction of the product lifetime will occur.

In addition, the LED light "PLANOX TUBE Farm" has operated actively in the chamber for the entirety of the test. No product damage was observed here.

Furthermore, the cleaning distance is regarded as suitable for the cleaning of animal houses.

Table 1: Overview of results

Test result	Evaluation*
Resistance to ammonia of the luminaire housing	
resistant	+
Cleaning distance	
Minimum distance with flat spray nozzel: 5 cm	+ +
Ingress of water into the housing without damages: No	+

Evaluation scheme

Test result	Evaluation*
Resistance to ammonia	
resistant	+
partly resistant	0
non-resistant	-
Ingress of water into the housing without damages	
no/yes	+/-
Cleaning distance	
5 cm	+ +
10 cm	+
15 cm	0
20 cm	-
25 cm	

* Evaluation range: + + / + / O / - / - - (O = standard, n.a. = not evaluated)

The Product

Manufacturer and applicant

RZB Rudolf Zimmermann, Bamberg GmbH Rheinstraße 16 96052 Bamberg Deutschland

Product: LED light "PLANOX TUBE Farm"

Contact: Phone +49 (0)951 7909-0 Fax +49 (0)951 7909-198 info@rzb-leuchten.de www.rzb.de

Description and technical data

The tested LED light "PLANOX TUBE Farm" is suitable for any usage in animal housing surroundings. The "PLANOX TUBE Farm" is also suitable for use in areas where an increased amount of ammonia and dust needs to be expected. Depending on the application, both borosilicate glass (special model) and PMMA are available as housing or diffuser material.

Table 2:

Technical data (according to manufacturer)

	PLANOX TUBE Farm			
	601066.002.5	601067.002.5	601068.002.5	601069.002.5
Electrical connection				
Voltage	220-240 V			
Frequency	50-60 Hz			
Performance	23 W	33 W	45 W	55 W
Dimension and weight				
Length	685 mm	965 mm	1,245 mm	1,530 mm
Diameter	78 mm			
Weight	ca. 1.4 kg	ca. 2.0 kg	ca. 2.3 kg	ca. 2.7 kg
Additional technical data				
Number of LED modules	2	3	4	5
Housing material	diffuser: PMMA, side panels: polyamide			
Colour temperature	4,000 K			
Dimmable	optional via DALI			
Light angle	ca. 120°			
Light yield	ca. 126 lm/W	ca. 133 lm/W	ca. 131 lm/W	ca. 135 lm/W

The Method

Resistance to ammonia

The ammonia resistance of the LED light "PLANOX TUBE Farm" was determined by a laboratory test with two luminaires according to the patented DLG test standard for agricultural use. The laboratory test is designed to replicate the conditions of a usage period of about 10 years exposure to animal living areas.

The test was carried out in a climate chamber under the following climate conditions:

Test duration	1500 h
Air temperature	70 °C
Relative humidity	70 %
Ammonia concentration	750 ppm

For assessing the ammonia resistance, each luminaire was examined visually, gravimetrically and the plastic parts additionally through measurement of the hardness (Shore D) before and after the climate testing. Since 2017, luminaires have additionally been following a cycle of operation predefined by DLG (3 hours on, 1 hour off) in order to eveluate any thermal impacts caused by switch-on and -off procedures during ammonia fumigation.

In order to avoid overheating (> 70 °C), the luminaires could be operated at a reduced power level during the testing period.

Cleaning distance

During test bench examinations of the mechanical resistance to high-pressure cleaners, the minimum cleaning distance was determined.

The minimum cleaning distance is defined as the distance between nozzle and surface when no damages can be observed at the housing surface.

The test was conducted under the conditions presented in table 3.

Table 3:

Test conditions cleaning distance

Line pressure	~150 bar
Water	cold, approx. 1,000 l/h, no detergents
Nozzle type	Flat spray nozzle, 25°
Exposition time	1 minute
Distance	250 mm, 200 mm, 150 mm, 100 mm, 50 mm
Ambient temperature	10°C

For all test procedures, the LED light "PLANOX TUBE Farm" with PMMA housing material in length of 685 mm and 1,530 mm has been used. After the tests, the luminaires underwent visual examination to a reference sample that was identical in construction.

Resistance to ammonia

Visual test

The comparative visual examination after the ammonia exposure has shown minor discolorations at the luminaire housing and LED battens. However, no negative impact on the luminaire performance needs to be expected.

During the test, the tube light appeared to be sufficiently gas-tight. Nevertheless it cannot be ruled out, that a limited ammount of ammonium compounds could enter the luminaire housing. Again, no negative impact on the luminaire performance needs to be expected.

The defects are rated as insignificant. The examination of the manufacturer's mounting parts didn't also show any defects.

Gravimetric test

Weight comparisions before and after the ammonia fumigation have not shown any measurable increases or decreases in weight.

Hardness test

During the hardness test (Shore D) no measurable changes were observed. All determined changes were within the measurement incertainty.

Based on the results of these tested parameters, the luminaire is evaluated as resistant to ammonia.

Cleaning distance

Even at a cleaning distance of only 50 mm, no damages to the luminaire could be observed. At no time a water ingress into the luminaires was noticed.

In order to avoid damage to the luminaires during cleaning reliably, according to the manufacturer's specifications a minimum cleaning distance of 10 cm should always be ensured.

Functional test

No defects were observed. All luminaires worked after the conducted tests.

Summary

The results show that the LED light "PLANOX TUBE Farm" fulfills the testing requirements for ammonia resistance and cleaning distance (evaluation "o" or better) and thus receives the test mark DLG-Approved. It can be expected that the luminaire is resistant to ammonical air in animal living areas and that no accelerated reduction of the product lifetime occurs.

A cleaning distance at 5 cm is possible for that type of luminaire. It is rated to hold a distance of at least 10 cm.

The LED light "PLANOX TUBE Farm" was operated both passively and actively during the ammonia fumigation in the test chamber and passed both tests successfully.

Other critera have not been assessed.

More information

Testing agency

DLG TestService GmbH, Gross-Umstadt location The tests are conducted on behalf of DLG e.V.

DLG test framework

DLG-Approved Test "Ammonia resistance" (current as of 07/2018)

Department

Agriculture

Division head

Dr. Ulrich Rubenschuh

Test engineer(s)

Dipl-Ing (FH) Tommy Pfeifer*

Author

DLG – the open network and professional voice

Founded in 1885 by the German engineer Max Eyth, DLG (Deutsche Landwirtschafts-Gesellschaft – German Agricultural Society) is an expert organisation in the fields of agriculture, agribusiness and the food sector. Its mission is to promote progress through the transfer of knowledge, quality standards and technology. As such, DLG is an open network and acts as the professional voice of the agricultural, agribusiness and food sectors.

As one of the leading organisations in the agricultural and food market, DLG organises international trade fairs and events in the specialist areas of crop production, animal husbandry, machinery and equipment for farming and forestry work as well as energy supply and food technology. DLG's quality tests for food, agricultural equipment and farm inputs are highly acclaimed around the world.

For more than 130 years, our mission has also been to promote dialogue between academia, farmers and

the general public across disciplines and national borders. As an open and independent organisation, our network of experts collaborate with farmers, academics, consultants, policymakers and specialists in administration in the development of futureproof solutions for the challenges facing the agriculture and the food industry.

Leaders in the testing of agricultural equipment and input products

The DLG Test Center Technology and Farm Inputs and its test methods, test profiles and quality seals hold a leading position in testing and certifying equipment and inputs for the agricultural industry. Our test methods and test profiles are developed by an independent and impartial commission to simulate in-field applications of the products. All tests are carried out using state-of-the-art measuring and test methods applying also international standards.

Internal test code DLG: 18-00019 Copyright DLG: © 2019 DLG



DLG TestService GmbH Gross-Umstadt location

Max-Eyth-Weg 1 • 64823 Groß-Umstadt • Germany Phone: +49 69 24788-600 • Fax: +49 69 24788-690 Tech@DLG.org • www.DLG.org Download of all DLG test reports free of charge at: www.DLG-Test.de